



Complete range of configurable and connected solar flood lights upto 15,000 lumens.

Tango G2 Gen 4.0 Solar

Comprehensive range of solar flood lights starting from 5,000 lumens to 15,000 lumens, with 125 lm/w efficacy, and the option of hybrid versions. Suitable for area lighting, billboards, facades and parking areas. configurable dimming profile and load wattage.

Benefits

- Brings light to areas without access to electric grid
- Environment friendly
- Saves energy
- High efficacy reduces cost per light point by reducing battery and panel size
- Preserves landscape as no trenching for cabling required
- Sturdy construction for long life
- Smart-city-ready for sustainable cities

Features

- High luminous efficacy of 125 lm/Watt.
- Configurable dimming profile and load wattage
- Compatible with multiple battery types (LiFePO4, LMLA GEL)
- Pressure die-cast aluminium housing for sturdiness and excellent thermal management
- Available in both off-grid and hybrid versions

Tango G2 Gen 4.0 Solar

Application

- Area lighting
- Advertising hoardings
- Facade
- Parking areas.

Versions

