



# GentleSpace Gen3

## BY481P LED350S/840 PSD WB PC SI

New Highbay - 840 neutral white - Power supply unit with DALI interface - Wide beam - Silver RAL 9006

With the third generation of the GentleSpace high-bay luminaire, we continue to bring innovations to the market by offering adaptable high bay lighting solutions for high ceiling and industrial applications. GentleSpace gen3 offers a wide variety of options in terms of optics and beam angles (from very narrow to wide), a choice of mounting possibilities and cover materials and a variety of lumen packages. This means that GentleSpace gen3 can easily help you create a tailor-made and ideal lighting solution for almost any high ceiling and/or industrial application. It can also support changes in application requirements (such as layout changes) thanks to its flexible optical system, which can be easily adjusted even after installation. In addition, GentleSpace gen3 also provides the option of advanced connectivity and is ready to be connected to IoT-based systems and software applications such as the Interact Industry. Overall, whether you are looking for a reliable 'fit and forget' solution, or one that can be adapted and controlled after installation, GentleSpace gen3 is the ideal solution for your application.

### Product data

General Information		Control interface	
Beam angle of light source	114 °	Control interface	DALI
Light source colour	840 neutral white	Connection	CE [ External connector]
Light source replaceable	Yes	Cable	Cord with plug Wieland/Adels compatible 5-pole
Number of gear units	1 unit	Protection class IEC	Safety class I (I)
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Glow-wire test	850/5 [ Temperature 850 °C, duration 5 s]
Driver included	Yes	Flammability mark	D [ For mounting on easily flammable surfaces]
Optic type	WB [ Wide beam]	CE mark	CE mark
Luminaire light beam spread	42° x 44°	ENEC mark	ENEC mark

## GentleSpace Gen3

Warranty period	5 years
Constant light output	No
Number of products on MCB (16 A type B)	8
EU RoHS compliant	Yes
Product family code	BY481P [ New Highbay]
Unified glare rating CEN	Not applicable

### Operating and Electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	15.3 A
Inrush time	0.061 ms
Power factor (min.)	0.9

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	Steel
Optical cover/lens finish	Clear
Overall length	600 mm
Overall width	490 mm
Overall height	85 mm
Colour	Silver RAL 9006
Dimensions (height x width x depth)	85 x 490 x 600 mm (3.3 x 19.3 x 23.6 in)

### Approval and Application

Ingress protection code	IP65 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]

### Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	35000 lm
-------------------------------------	----------

Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	4000 K
Init. colour rendering index	>80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	230 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)


Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L90
Lumen maintenance at median useful life* 100,000 h	L80

### Application Conditions


Ambient temperature range	-30 to +45 °C
Performance ambient temperature Tq	45 °C
Maximum dimming level	10%
Suitable for random switching	No

### Product Data

Full product code	871869940793300
Order product name	BY481P LED350S/840 PSD WB PC SI
EAN/UPC – product	8718699407933
Order code	40793300
SAP numerator – quantity per pack	1
SAP numerator – packs per outer box	1
Material no. (12 NC)	910500465599
SAP net weight (piece)	11.000 kg





## Dimensional drawing



GentleSpace gen3 BY480P-BY483P

Photometric data



IFGU1\_BY481PPSD1xLED350S840WB

OFPC1\_BY481PPSD1xLED350S840WB

