



CoreLine Trunking

LL121X 5X2.5 WH BC

CoreLine Trunking - 5 conductors cross-section 2.5 mm² - White
- Blind cover

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Product data

| General Information | |
|--------------------------|--|
| Protection class IEC | Safety class I (I) |
| CE mark | CE mark |
| Material | Steel |
| Mechanical accessories | BC [Blind cover] |
| Angle | - |
| Accessory colour | White |
| Product family code | LL121X [CoreLine Trunking] |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Input frequency | 50 to 60 Hz |
| Circuit option | 5x2.5 [5 conductors cross-section 2.5 mm ²] |
| Mechanical and Housing | |
| Overall length | 1730 mm |
| Overall width | 81 mm |
| Overall height | 43 mm |

| Colour | White |
|-------------------------------------|---|
| Dimensions (height x width x depth) | 43 x 81 x 1730 mm (1.7 x 3.2 x 68.1 in) |
| Approval and Application | |
| Ingress protection code | IP20 [Finger-protected] |
| Mech. impact protection code | IK02 [0.2 J standard] |
| Application Conditions | |
| Ambient temperature range | -20 to +35 °C |
| Product Data | |
| Full product code | 871869634647100 |
| Order product name | LL121X 5X2.5 WH BC |
| EAN/UPC – product | 8718696346471 |
| Order code | 34647100 |
| Numerator – quantity per pack | 1 |
| Numerator – packs per outer box | 1 |
| SAP material | 910925863235 |

CoreLine Trunking

SAP net weight (piece)

2.040 kg

