



# CoreLine Trunking

## LL121X 7X2.5 WH BC

CoreLine Trunking - 7 conductors cross-section 2.5 mm<sup>2</sup> - White  
- Blind cover

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information	
Connection	C-2R [ Connector with 2 additional wires for light regulation]
Protection class IEC	Safety class I (I)
CE mark	CE mark
Material	Steel
Mechanical accessories	BC [ Blind cover]
Angle	-
Accessory colour	White
Product family code	LL121X [ CoreLine Trunking]
Operating and Electrical	
Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Circuit option	7x2.5 [ 7 conductors cross-section 2.5 mm <sup>2</sup> ]
Mechanical and Housing	
Overall length	1730 mm

Overall width	81 mm
Overall height	43 mm
Colour	White
Dimensions (height x width x depth)	43 x 81 x 1730 mm (1.7 x 3.2 x 68.1 in)
Approval and Application	
Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]
Application Conditions	
Ambient temperature range	-20 to +35 °C
Product Data	
Full product code	871869634649500
Order product name	LL121X 7X2.5 WH BC
EAN/UPC – product	8718696346495
Order code	34649500
Numerator – quantity per pack	1

## CoreLine Trunking

---

Numerator – packs per outer box	1
SAP material	910925863237
SAP net weight (piece)	2.080 kg

---

