



DigiStreet

BGP760 LED12-/830 II DM11 DGR D9 62

DigiStreet Micro - LED Module 1200 lm - 830 warm white - Safety class II (II) - Distribution medium 11 - Dark gray - Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode - Spigot for diameter 62 mm

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product data

General Information	
Number of light sources	1 [1 pc]
Lamp family code	LED12 [LED Module 1200 lm]
Light source colour	830 warm white
Light source replaceable	Yes
Number of gear units	1 unit
Gear	EB [Electronic]
Driver/power unit/transformer	PSD [Power supply unit with DALI interface]
Driver included	Yes
Optical element	DF [Diffuser element]

Optical cover/lens type	FG [Flat glass]
Luminaire light beam spread	160° - 42° x 54°
Control interface	DALI
Connection	SI [Screw connection block]
Cable	-
Protection class IEC	Safety class II (II)
Glow-wire test	650/5 [Temperature 650 °C, duration 5 s]
Flammability mark	NO [-]
CE mark	CE mark
ENEC mark	ENEC mark

UL mark	-
Warranty period	5 years
Optic type outdoor	Distribution medium 11
Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Constant light output	No
Spare parts available	Yes
Number of products on MCB (16 A type B)	29
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
EU RoHS compliant	Yes
WEEE mark	WEEE mark
LED engine type	LED
Serviceability class	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Product family code	BGP760 [DigiStreet Micro]

Light Technical

Upward light output ratio	0
Standard tilt angle post-top	0°
Standard tilt angle side entry	0°

Operating and Electrical

Input Voltage	220-240 V
Input frequency	50 to 60 Hz
Inrush current	15 A
Inrush time	0.295 ms
Driver current	326 mA
Power factor (max.)	-
Power factor (min.)	0.96
Power factor (nom.)	0.89

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Housing material	Aluminum die-cast
Reflector material	Polycarbonate
Optic material	Acrylate
Optical cover/lens material	Glass

Fixation material	Stainless steel
Mounting device	62 [Spigot for diameter 62 mm]
Optical cover/lens shape	Flat
Optical cover/lens finish	Clear
Overall length	695 mm
Overall width	236 mm
Overall height	103 mm
Effective projected area	0.0578 m ²
Colour	Dark gray
Dimensions (height x width x depth)	103 x 236 x 695 mm (4.1 x 9.3 x 27.4 in)

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge protection (common/differential)	Luminaire surge protection level up to 6 kV differential mode and 8 kV common mode

Initial Performance (IEC Compliant)

Initial luminous flux	1092 lm
Luminous flux tolerance	+/-7%
Initial LED luminaire efficacy	103 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	80
Initial chromaticity	(0.43 0.40) SDCM <5
Initial input power	10.6 W
Power consumption tolerance	+/-11%

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 100,000 h	L97

Application Conditions

Ambient temperature range	-40 to +50 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	Not applicable

Product Data

Full product code	871869637680500
Order product name	BGP760 LED12-/830 II DM11 DGR D9 62
EAN/UPC – product	8718696376805
Order code	37680500
SAP numerator – quantity per pack	1
Numerator – packs per outer box	1
Material no. (12 NC)	910925863555
SAP net weight (piece)	5.727 kg




Dimensional drawing



DigiStreet BGP760-BTP764

Photometric data



OFPC1_BGP760T251xLED12-4S830DM11

