



# CoreLine Trunking

## LL120X LED160S/865 1x PSD MB 7 WH

CoreLine Trunking - 6 pcs - LED module, system flux 16000 lm - Power supply unit with DALI interface - Medium beam - - - 7 conductors - - - Feed-through wiring 7-phase - Ceiling-mounting bracket - White - - - -

Whether for a new facility or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Trunking range of LED products can be used to replace general lighting. The process of selecting, installing and maintaining is so easy – it's a simple switch.

### Product data

General Information		Connection	
Number of light sources	6 [ 6 pcs]	Cable	-
Lamp family code	LED160S [ LED module, system flux 16000 lm]	Protection class IEC	Safety class I (I)
Beam angle of light source	120 °	Mounting	SMB [ Ceiling-mounting bracket]
Light source colour	865 cool daylight	Ready-to-install	-
Light source replaceable	No	Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Number of gear units	1 unit	Flammability mark	F [ For mounting on normally flammable surfaces]
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Accessories included	MB-SW [ Mounting bracket for suspension wire]
Driver included	Yes	CE mark	CE mark
Optic type	MB [ Medium beam]	ENEC mark	ENEC mark
Optical cover/lens type	No [ -]	Mechanical accessories	No [ -]
Luminaire light beam spread	76° x 74°	Remarks	*- According to the Lighting Europe guidance paper 'Evaluating performance of LED based luminaires – January 2018': statistically there is
Emergency lighting	No [ -]		
Control interface	DALI		
Internal wiring	Standard		
Feed-through wiring	Feed-through wiring 7-phase		

## CoreLine Trunking

	no relevant difference in lumen maintenance between the B50 and, for example, the B10. Therefore, the median useful life (B50) value also represents the B10 value.
Constant light output	No
Number of products on MCB (16 A type B)	12
EU RoHS compliant	Yes
Product family code	LL120X [ CoreLine Trunking]
Unified glare rating CEN	Not applicable

### Light Technical

Light distribution	DIR [ Direct lighting]
--------------------	------------------------

### Operating and Electrical

Input Voltage	220 to 240 V
Input frequency	50 to 60 Hz
Control signal voltage	0-16 V DC DALI
Circuit	No [ -]
Circuit option	7 [ 7 conductors]
Initial CLO power consumption	- W
Average CLO power consumption	- W
Inrush current	4.8 A
Inrush time	2.3 ms
Power factor (min.)	0.97

### Controls and Dimming

Dimmable	Yes
----------	-----

### Mechanical and Housing

Housing material	Steel
Reflector material	-
Optic material	Acrylate
Optical cover/lens material	Acrylate
Fixation material	Steel
Optical cover/lens finish	Frosted
Overall length	3450 mm
Overall width	95 mm
Overall height	52 mm
Height	52 mm
Diameter	-

Colour	White
Dimensions (height x width x depth)	52 x 95 x 3450 mm (2 x 3.7 x 135.8 in)

### Approval and Application

Ingress protection code	IP20 [ Finger-protected]
Mech. impact protection code	IK02 [ 0.2 J standard]

### Initial Performance (IEC Compliant)

Initial luminous flux	16000 lm
Luminous flux tolerance	+/-2%
Initial LED luminaire efficacy	148 lm/W
Init. Corr. Colour Temperature	6500 K
Init. Colour rendering index	≥80
Initial chromaticity	(0.38, 0.38) SDCM <3
Initial input power	108 W
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Lumen maintenance at median useful life* 50,000 h	L80

### Application Conditions

Ambient temperature range	-20 to +35 °C
Performance ambient temperature Tq	25 °C
Maximum dimming level	1%
Suitable for random switching	No


### Product Data

Full product code	871869638189200
Order product name	LL120X LED160S/865 1x PSD MB 7 WH
EAN/UPC – product	8718696381892
Order code	38189200
Numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	910925864069
SAP net weight (piece)	7.130 kg



## CoreLine Trunking

### Dimensional drawing



CoreLine electr. units LL120X-LL122X

