



# GreenUp Highbay G2

## BY560P LED105/CW PSD/CL HRO

865 cool daylight - Power supply unit with DALI interface - High-rack optic

Height is not an issue any more, maximum 16 m movement detection together with the wireless ZigBee control, GreenUp HighBay G2, light up your space smartly.

### Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress and as such we strongly recommend that the environment in which the luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips/Signify cannot guarantee safe failure and product warranty will become void

### Product data

General Information			
Beam angle of light source	- °	Glow-wire test	650/5 [ Temperature 650 °C, duration 5 s]
Light source colour	865 cool daylight	Flammability mark	F [ For mounting on normally flammable surfaces]
Light source replaceable	No	CE mark	CE mark
Number of gear units	1 unit	ENEC mark	-
Driver/power unit/transformer	PSD [ Power supply unit with DALI interface]	Warranty period	3 years
Driver included	Yes	Constant light output	No
Optic type	HRO [ High-rack optic]	Number of products on MCB (16 A type B)	24
Optical cover/lens type	LIN-PC [ Linear-lens array in polycarbonate cover]	LED engine type	LED
Luminaire light beam spread	45° x 90°	<b>Operating and Electrical</b>	
Control interface	DALI	Input Voltage	220 to 240 V
Connection	Flying leads/wires	Input frequency	50 to 60 Hz
Cable	Cable 1.5 m without plug (C1K5)	Inrush current	5.1 A
Protection class IEC	Safety class I (I)	Inrush time	760 ms

# GreenUp Highway G2

Power factor (min.)	0.95
---------------------	------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Mechanical and Housing

Housing material	Aluminum extruded
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Optical cover/lens finish	Clear
Overall length	525 mm
Overall width	190 mm
Colour	Aluminum and white

## Approval and Application

Ingress protection code	IP40 [ Wire-protected]
Mech. impact protection code	IK03 [ 0.3 J]

## Initial Performance (IEC Compliant)

Initial luminous flux (system flux)	10500 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Init. Corr. Colour Temperature	6500 K
Init. Colour rendering index	>80

Initial chromaticity	(0.313,0.324)SDCM<5
Initial input power	75 W
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)


Median useful life L70B50	65000 h
Median useful life L80B50	45000 h
Median useful life L90B50	25000 h

## Application Conditions


Ambient temperature range	-20 to +45 °C
Maximum dimming level	1% (depends on dimmer, ELV)
Suitable for random switching	No

## Product Data

Full product code	911401502551
Order product name	BY560P LED105/CW PSD/CL HRO
Order code	01502551
Numerator – quantity per pack	1
SAP numerator – packs per outer box	2
Material no. (12 NC)	911401502551
Net Weight (Piece)	2.299 kg



## Dimensional drawing



GreenUp High-bay BY550P/BY550X

## GreenUp Highbay G2

