



# RoadFlair

## BRP390 LED70/WW 52W 220-240V DM

Designed for major and city roads, Philips RoadFlair is a new and exciting product set to brighten your streets beyond imagination. Smartly-designed to bring cities the highest savings possible with best-in-class lumen per watt, this road lighting production comes at a competitive price bound to excite. Philips RoadFlair brings energy efficiency, improves a city's sustainability drive and delivers significant cost reduction in urban environments. The right road luminaire coupled with the right lighting application will create the best environment for your municipality, benefiting local communities and boosting tourism and businesses.

### Product data

General Information	
Light source colour	730 warm white
Light source replaceable	No
Driver included	Yes
Optical cover/lens type	PC-MLO [ Polycarbonate micro lens optic]
Control interface	-
Connection	Mains outlet socket
Cable	Cable 0.5 m without plug
Protection class IEC	Safety class I (I)
Flammability mark	NO [ -]
CE mark	CE mark
ENEC mark	-
Light source engine type	LED
Serviceability class	Class B, the luminaire is equipped with some serviceable parts (when applicable): driver, control units, surge-protection device, front cover and mechanical parts

Light Technical	
Standard tilt angle post-top	-
Standard tilt angle side entry	-
Operating and Electrical	
Input Voltage	220 to 240 V
Input frequency	50 or 60 Hz
Power factor (min.)	0.9
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Housing material	Aluminum die-cast
Optical cover/lens material	Polycarbonate
Mounting device	48/60S [ Side-entry for diameter 48-60 mm]
Optical cover/lens shape	Ball, globular
Optical cover/lens finish	Frosted
Overall length	402 mm

## RoadFlair

Overall width	156 mm
Overall height	85 mm
Colour	Gray

### Approval and Application

Ingress protection code	IP66 [ Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [ 5 J vandal-protected]

### Initial Performance (IEC Compliant)

Initial luminous flux	7030 lm
Luminous flux tolerance	+/-10%
Initial LED luminaire efficacy	140 lm/W
Init. Corr. Colour Temperature	3000 K
Init. Colour rendering index	>70
Initial chromaticity	38 SDCM
Initial input power	52 W

Power consumption tolerance	+/-10%
-----------------------------	--------

### Application Conditions


Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Product Data

Full product code	911401865298
Order product name	BRP390 LED70/WW 52W 220-240V DM
Order code	01865298
Numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	911401865298
SAP net weight (piece)	2.799 kg



## Dimensional drawing



BRP391/392/393/394 RoadFlair

