



OccuSwitch

LRM1080/00 Sensr Mov Det St Ir

Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced


Movement detector with a built-in switch - up to 6 A - controls max 25 m² area - Advanced

Product data

Product Data	
Full product code	871155973140799
Order product name	LRM1080/00 SENSR MOV DET ST IR
EAN/UPC - product	8711559731407
Order code	73140799
SAP numerator - quantity per pack	1

Numerator - packs per outer box	42
Material no. (12 NC)	913700327903
SAP net weight (piece)	0.200 kg

Dimensional drawing



LRM1080/00 SENSR MOV DET ST IR