



Dynalite Leading Edge Dimmers

DLE410

4 channel Leading Edge Dimmer Controller with a maximum load per channel of 10 A.


The Philips Dynalite DLE410 is a four channel leading edge dimmer controller, with a maximum load per channel of 10 A. - It is suitable for use with incandescent, neon and selected fluorescent light sources, as well as iron core and leading edge electronic transformers. - Ideal for applications where multiple user settings are required
Interference suppression
Naturally ventilated
Soft start and voltage regulation technologies
Diagnostic functionality
User controls
Options available

Product data


General Information		Order product name	DLE410
CE mark	CE mark	EAN/UPC – product	8710163505268
Remarks	Please download the Lighting - Product Data Sheet for more information and ordering options	Order code	50526800
EU RoHS compliant	Yes	SAP numerator – quantity per pack	1
		SAP numerator – packs per outer box	1
		Material no. (12 NC)	913703006009
		SAP net weight (piece)	8.450 kg
Application Conditions			
Ambient temperature range	0 to +40 °C		
Product Data			
Full product code	871016350526800		

Dynalite Leading Edge Dimmers

Dimensional drawing



Dynalite Leading Edge Dimmers



Dynalite Leading Edge Dimmers

