



BT-ALU EM ballasts for TL Fluorescent lamps

BT-ALU 18W 220V C 'SC



Affordable, reliable, long-life electromagnetic ballast for TL-D fluorescent lamps; ideal solution for economical high-quality performance

Product data

General Information		Temperature	
Application code	18W	T-winding (max.)	130 °C
Design	C	Delta-T normal conditions	65 °C
Operating and Electrical		Mechanical and Housing	
Input Voltage	220 V	Housing	L 155x39x28
Input frequency	50 Hz		
Power factor 100% load (min.)	0.85	Approval and Application	
Input current with PF correction	0.12 A	Energy efficiency index	C
Input current without PF Correction	0.31 A	Approval marks	CCC certificate
Power factor with PF compensation	0.35	Product Data	
Power losses (nom.)	8.2 W	Full product code	872790085753500
Wiring		Order product name	BT-ALU 18W 220V C SC
Connector type	Screw	EAN/UPC – product	8711500998101
System characteristics		Order code	85753500
Rated ballast-lamp power	18 W	SAP numerator – quantity per pack	1
		Numerator – packs per outer box	32
		SAP material	913710124850
		SAP net weight (piece)	0.528 kg

BT-ALU EM ballasts for TL Fluorescent lamps

Dimensional drawing



BT-ALU 18W 220V C 'SC

Product

BT-ALU 18W 220V C SC

