



MASTER MHN-SA

MASTER MHN-SA 1800W/956 230V XW UNP/1

Compact quartz metal halide lamps with double-pinch

Warnings and Safety

- Use only in totally enclosed luminaire, even during testing (IEC61167, IEC 62035, IEC60598)
- The luminaire must be able to contain hot lamp parts if the lamp ruptures
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data

General Information	
Cap base	X830R [X830R]
Operating position	P15 [Parallel +/-15D or Horizontal(HOR)]
Life to 5% failures (nom.)	1800 h
Life to 10% failures (nom.)	2300 h
Life to 20% failures (nom.)	3000 h
Life to 50% failures (nom.)	5000 h
Light Technical	
Colour Code	956 [CCT of 5,600 K]
Luminous flux (rated) (nom.)	155000 lm
Colour designation	Daylight
Lumen maintenance 1,000 hours (nom.)	92 %
Lumen maintenance 2,000 hours (nom.)	80 %
Lumen maintenance 5,000 hours (nom.)	60 %
Chromaticity coordinate X (nom.)	330
Chromaticity coordinate Y (nom.)	339
Correlated Colour Temperature (Nom)	5600 K
Luminous efficacy (rated) (nom.)	86 lm/W

Colour rendering index (nom.)	86
Operating and Electrical	
Lamp supply voltage	230 V [230]
Power (Rated) (Nom)	1800.0 W
Lamp current run-up (max.)	25 A
Lamp current (EM) (nom.)	17.3 A
Ignition supply voltage (min.)	198 V
Voltage (Max)	130 V
Voltage (Min)	110 V
Voltage (Nom)	120 V
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Lamp Finish	Clear
Cap-base information	na [-]

MASTER MHN-SA

Approval and Application

Energy efficiency label (EEL)	A+
Mercury (Hg) content (nom.)	92 mg
Energy consumption kWh/1,000 hours	1980 kWh

Luminaire Design Requirements


Bulb temperature (max.)	980 °C
Pinch temperature (max.)	300 °C

Product Data

Full product code	871150020106500
-------------------	-----------------

Order product name	MASTER MHN-SA 1800W/956 230V XW UNP/1
EAN/UPC – product	8718291548294
Order code	20106500
Numerator – quantity per pack	1
Numerator – packs per outer box	1
SAP material	928099205130
SAP net weight (piece)	110.000 g
ILCOS code	MN-1800-H-X830R-/H


Dimensional drawing



MHN-SA 1800W/956 230V XW

Product	D (max)	O	X	A	C (max)
MASTER MHN-SA 1800W/956 230V XW UNP/1	41 mm	25 mm	25 mm	318 mm	369 mm


Photometric data




LDPO_MHN-SA_1800W_230V-Spectral power distribution Colour

MASTER MHN-SA

Lifetime



MHN SA 1800W 956 Life Expectancy Diagram



MHN SA 1800W 956 Lumen Maintenance Diagram

