



MSR Gold™ MiniFastFit (Touring/ Stage)

MSR Gold™ 400 MiniFastFit 1CT/16

Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Product data


General Information		Operating and Electrical	
Cap base	PGJX28 [PGJX28]	Power (Rated) (Nom)	400 W
Operating position	UNIVERSAL [Any or Universal (U)]	Lamp current (nom.)	7.2 A
Main application	Entertainment	Ignition supply voltage (min.)	198 V
Life to 50% failures (nom.)	750 h	Chromaticity coordinate X (nom.)	310
System description	MiniFastFit	Chromaticity coordinate Y (nom.)	320
Colour Code	- [Not Specified]	Correlated Colour Temperature (Nom)	6700 K
Luminous flux (min.)	23400 lm	Luminous efficacy (rated) (nom.)	65 lm/W
Luminous flux (nom.)	26000 lm	Colour rendering index (nom.)	60

MSR Gold™ MiniFastFit (Touring/Stage)

Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Cap-base information	PGJX28
Luminaire Design Requirements	
Bulb temperature (max.)	950 °C
Pinch temperature (max.)	500 °C
Product Data	
Full product code	871829115828800

Order product name	MSR Gold™ 400 MiniFastFit 1CT/16
EAN/UPC – product	8718291158288
Order code	15828800
Numerator – quantity per pack	1
SAP numerator – packs per outer box	16
Material no. (12 NC)	928194005114
Net Weight (Piece)	0.053 kg

Dimensional drawing



MSR GOLD 400 MiniFastFit

Product	D (max)	O (min)	L (min)	L (max)	L (max)	C (max)	F (max)	F (max)	F (min)
MSR Gold™ 400 MiniFastFit 1CT/16	23.2 mm	3.0 mm	55 mm	57 mm	56 mm	111 mm	36.5 mm	36 mm	35.3 mm

