



CorePro LEDspot MV

Corepro LEDspot 4.6-50W GU10 827 36D

CorePro LEDspots are a perfect fit for spot lighting and deliver warm halogen-like light. They are compatible with most existing fixtures with a GU10 or E14 holder and are designed as a retrofit replacement for halogen or incandescent spots. LEDlamps deliver huge energy savings and minimize maintenance cost.

Product data

General Information		Lamp current (nom.)	
Cap base	GU10 [GU10]		39 mA
EU RoHS compliant	Yes	Wattage equivalent	50 W
Nominal lifetime (nom.)	15000 h	Starting time (nom.)	0.5 s
Switching cycle	50,000X	Warm-up time to 60% light (nom.)	0.5 s
Technical type	4.6-50W	Power factor (nom.)	0.5
		Voltage (Nom)	220-240 V
Light Technical		Temperature	
Colour Code	827 [CCT of 2,700 K]	T-Case maximum (nom.)	72 °C
Beam Angle (Nom)	36 °		
Luminous flux (nom.)	355 lm	Controls and Dimming	
Luminous intensity (nom.)	700 cd	Dimmable	No
Colour designation	Warm White (WW)		
Correlated Colour Temperature (Nom)	2700 K	Approval and Application	
Luminous efficacy (rated) (nom.)	77.00 lm/W	Energy efficiency label (EEL)	A+
Colour consistency	<6	Suitable for accent lighting	Yes
Colour rendering index (nom.)	80	Energy consumption kWh/1,000 hours	5 kWh
LLMF at end of nominal lifetime (nom.)	70 %		
Luminous flux in 90° cone (rated)	355 lm	Product Data	
		Full product code	871869675251700
		Order product name	Corepro LEDspot 4.6-50W GU10 827 36D
		EAN/UPC – product	8718696752517
		Order code	75251700
Operating and Electrical			
Input frequency	50 to 60 Hz		
Power (Rated) (Nom)	4.6 W		

CorePro LEDspot MV

Numerator – quantity per pack	1
SAP numerator – packs per outer box	10
Material no. (12 NC)	929001215232

Net Weight (Piece)	0.036 kg
--------------------	----------



Dimensional drawing



Product	D	C
Corepro LEDspot 4.6-50W GU10 827 36D	50 mm	54 mm


LEDClassic 50W GU10 WW 230V 36D ND 1BC/6

Photometric data



LEDspotMV GU10 MR16 827


LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D



LED Lamps, CorePro LEDspotMV 4.6-50W GU10 PAR16 827 355lm 36D

CorePro LEDspot MV

Lifetime



CLA LEDspotMV 50W GU10 827 36D ND

CLA LEDspotMV 50W GU10 827 36D ND

