



MASTER LEDtube EM/ Mains

MASTER LEDtube 1200mm UO 16W 865 T8

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

• -

Product data

General Information	
Cap base	G13 [Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	50000 h
Switching cycle	200,000X

Light Technical	
Colour Code	865 [CCT of 6,500 K]
Beam Angle (Nom)	160 °
Luminous flux (nom.)	2500 lm
Colour designation	Cool Daylight
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	156.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	16 W
Lamp current (max.)	75 mA
Lamp current (min.)	68 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T-ambient (max.)	35 °C
T-ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	55 °C

MASTER LEDtube EM/Mains

Controls and Dimming

Dimmable No

Mechanical and Housing

Product length 1200 mm

Approval and Application

Energy efficiency label (EEL) A++

Energy-saving product Yes


Approval marks CE marking RoHS compliance KEMA Keur certificate

Energy consumption kWh/1,000 hours 16 kWh

Product Data

Full product code	871869668740600
Order product name	MASTER LEDtube 1200mm UO 16W 865 T8
EAN/UPC – product	8718696687406
Order code	68740600
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001298002
SAP net weight (piece)	0.251 kg


Dimensional drawing




TLED 4ft 16W-36W 2500lm 160D 6500K G13ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm UO 16W 865 T8	25.78 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data



LEDtube 1200mm UO 16W 865 T8



LEDtube 1200mm UO 16W 865 T8

MASTER LEDtube EM/Mains

Photometric data



LEDtube 600mm 1200mm 1500mm UO T8

Lifetime



LEDtube 600mm 1200mm 1500mm UO T8



LEDtube 600mm 1200mm 1500mm UO T8

