



# MASTER LEDspot MV

## Master LED 4.9-50W GU10 927 36D Dim

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information	
Cap base	GU10 [ GU10]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	5-50W
Luminous intensity (nom.)	650 cd
Colour designation	Warm White (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	80.61 lm/W
Colour consistency	<6
Colour rendering index (nom.)	90
LLMF at end of nominal lifetime (nom.)	70 %
Luminous flux in 90° cone (rated)	355 lm
Operating and Electrical	
Input frequency	50 to 60 Hz

# MASTER LEDspot MV

Power (Rated) (Nom)	5 W
Lamp current (nom.)	27 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.8
Voltage (Nom)	220-240 V

## Temperature

T-Case maximum (nom.)	80 °C
-----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application


Energy efficiency label (EEL)	A+
-------------------------------	----

Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	5 kWh

## Product Data

Full product code	871869670731900
Order product name	Master LED 4.9-50W GU10 927 36D Dim
EAN/UPC – product	8718696707319
Order code	70731900
Numerator – quantity per pack	1
SAP numerator – packs per outer box	10
Material no. (12 NC)	929001348808
Net Weight (Piece)	0.038 kg


## Dimensional drawing




GU10 230V5W-50W 345lm 36D 2700K GU10 Dim

Product	D	C
Master LED 4.9-50W GU10 927 36D Dim	50 mm	54 mm

## Photometric data



MASTER LEDspotMV 50W GU10 927 36D 355lm



MASTER LEDspotMV 35W GU10 927 36D 260lm

# MASTER LEDspot MV

## Photometric data



MASTER LEDspotMV 50W GU10 36D 355lm

## Lifetime



MASTER LEDspotMV GU10 922-927 36D

MASTER LEDspotMV GU10 922-927 36D

