



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 20W 15D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	20-35W
Light Technical	
Colour Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	15 °
Luminous flux (nom.)	1850 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	92.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz


Power (Rated) (Nom)	20 W
Lamp current (nom.)	95 mA
Wattage equivalent	35 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	67 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	20 kWh

# MASTER LEDspot PAR High Lumen

Product Data	
Full product code	871869673129100
Order product name	Master LED PAR30L 20W 15D 840
EAN/UPC – product	8718696731291
Order code	73129100
Numerator – quantity per pack	1

SAP numerator – packs per outer box	6
Material no. (12 NC)	929001353908
Net Weight (Piece)	0.410 kg


## Dimensional drawing




PAR30L 220-240V 20-35W 1850lm 4KK E27 ND

Product	D	C
Master LED PAR30L 20W 15D 840	95.5 mm	129 mm


## Photometric data



LEDspot PAR30L E27 20W 4000K 15D



LEDspot PAR30L E27 20W 4000K 15D



LEDspot PAR30L E27 20W 4000K 15D

# MASTER LEDspot PAR High Lumen

## Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

