



# MASTER LEDspot PAR High Lumen

## Master LED PAR30L 32W 30D 840

Philips High Lumen PAR30L integrates a leading COB LED light source and a compact high-efficiency driver into a traditional CDM PAR30L form-factor. It brings out the beauty in merchandise with brighter, high-performance lighting. Additionally, the lamp features an over temperature protection (OTP) to ensure a long operating life time.

### Product data

General Information	
Cap base	E27 [ E27]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	25000 h
Switching cycle	50,000X
Technical type	32-50W
Light Technical	
Colour Code	841 [ CCT of 4100K (841)]
Beam Angle (Nom)	30 °
Luminous flux (nom.)	3000 lm
Colour designation	Cool White (CW)
Correlated Colour Temperature (Nom)	4000 K
Luminous efficacy (rated) (nom.)	93.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	82
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz

Power (Rated) (Nom)	32 W
Lamp current (nom.)	160 mA
Wattage equivalent	50 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	79 °C
Controls and Dimming	
Dimmable	No
Approval and Application	
Energy efficiency label (EEL)	A+
Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	32 kWh


# MASTER LEDspot PAR High Lumen

## Product Data

Full product code	871869673146800
Order product name	Master LED PAR30L 32W 30D 840
EAN/UPC – product	8718696731468
Order code	73146800
Numerator – quantity per pack	1

SAP numerator – packs per outer box	6
Material no. (12 NC)	929001354808
Net Weight (Piece)	0.410 kg


## Dimensional drawing




PAR30L 220-240V 32-70W 30D 4000K E27 ND

Product	D	C
Master LED PAR30L 32W 30D 840	95.5 mm	129 mm

## Photometric data




Access Lighting - Spot  
1 - PAR30L 32W 30D 840  
Access Lighting E27  
Page 10



LEDspot PAR30L E27 32W 4000K 30D

LEDspot PAR30L E27 32W 4000K 30D



LEDspot PAR30L E27 32W 4000K 30D

# MASTER LEDspot PAR High Lumen

## Lifetime



LEDspot MAS 37W E27 PAR30L 830 15D ND



LEDspot MAS 37W E27 PAR30L 830 15D ND

