

MASTER LEDtube EM/ Mains

MASTER LEDtube 1200mm 14W 865 T8 THD

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance which cannot be distinguished from traditional fluorescent. For those that are looking for value for money within limited budget and re-lamping efforts for better light effect and lifetime.

Warnings and Safety

• -

Product data

General Information		Operating and Electrical	
Cap base	G13 [Medium Bi-Pin Fluorescent]	Input frequency	50 to 60 Hz
EU RoHS compliant	Yes	Power (Rated) (Nom)	14 W
Nominal lifetime (nom.)	50000 h	Lamp current (max.)	73 mA
Switching cycle	50,000X	Lamp current (min.)	54 mA
Light Technical		Starting time (nom.)	0.5 s
Colour Code	865 [CCT of 6,500 K]	Warm-up time to 60% light (nom.)	0.5 s
Beam Angle (Nom)	160 °	Power factor (nom.)	0.9
Luminous flux (nom.)	2100 lm	Voltage (Nom)	220-240 V
Colour designation	Cool Daylight	Temperature	
Correlated Colour Temperature (Nom)	6500 K	T-ambient (max.)	45 °C
Luminous efficacy (rated) (nom.)	150.00 lm/W	T-ambient (min.)	-20 °C
Colour consistency	<6	T storage (max.)	65 °C
Colour rendering index (nom.)	83	T storage (min.)	-40 °C
LLMF at end of nominal lifetime (nom.)	70 %	T-Case maximum (nom.)	55 °C

MASTER LEDtube EM/Mains

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Product length	1200 mm
----------------	---------


Approval and Application

Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	CE marking RoHS compliance KEMA Keur certificate
Energy consumption kWh/1,000 hours	14 kWh

Product Data

Full product code	871869672859800
Order product name	MASTER LEDtube 1200mm 14W 865 T8 THD
EAN/UPC – product	8718696728598
Order code	72859800
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929001375308
SAP net weight (piece)	0.215 kg


Dimensional drawing




TLED 4ft 220-240V14W-36W 6500K G13 ND

Product	D1	D2	A1	A2	A3
MASTER LEDtube 1200mm 14W 865 T8 THD	25.8 mm	28 mm	1198.2 mm	1205.3 mm	1212.4 mm

Photometric data




LEDtubes, TLED T12 120-277V 20W 6500K G13



MAS LEDtube EM 14W G13 765 T8 THD


MASTER LEDtube EM/Mains

Photometric data




MAS LEDtube EM 14W G13 740 T8 THD


Lifetime




MAS LEDtube EM 14W G13 740-765 T8 THD



MAS LEDtube EM 14W G13 740-765 T8 THD




MAS LEDtube EM 14W G13 740-765 T8 THD



MAS LEDtube EM 14W G13 740-765 T8 THD

MASTER LEDtube EM/Mains

Lifetime



MAS LEDtube EM 14W G13 740-765 T8 THD

