



# Master Value LEDtube T8

## MASTER LEDtube VLE 1500mm HO 20.5W 865 T8

A high-performance LED solution, the professional Master Value LED tube is ideal for replacing T8 fluorescent lamps using EM ballast or installing directly on the mains. This product provides a uniform lighting effect for use in all general lighting, as well as instant energy-efficiency, making for an environmentally friendly solution.

### Product data

General Information	
Cap base	G13 [ Medium Bi-Pin Fluorescent]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	50000 h
Switching cycle	200,000X

Light Technical	
Colour Code	865 [ CCT of 6,500 K]
Beam Angle (Nom)	240 °
Luminous flux (nom.)	3100 lm
Colour designation	Cool Daylight
Correlated Colour Temperature (Nom)	6500 K
Luminous efficacy (rated) (nom.)	151.00 lm/W
Colour consistency	<6
Colour rendering index (nom.)	83
LLMF at end of nominal lifetime (nom.)	70 %

Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	20.5 W

Lamp current (max.)	97 mA
Lamp current (min.)	89 mA
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.9
Voltage (Nom)	220-240 V

Temperature	
T-ambient (max.)	45 °C
T-ambient (min.)	-20 °C
T storage (max.)	65 °C
T storage (min.)	-40 °C
T-Case maximum (nom.)	60 °C

Controls and Dimming	
Dimmable	No


Mechanical and Housing	
Bulb material	Glass

# Master Value LEDtube T8

Product length	1500 mm
<b>Approval and Application</b>	
Energy efficiency label (EEL)	A++
Energy-saving product	Yes
Approval marks	RoHS compliance CE marking KEMA Keur certificate
Energy consumption kWh/1,000 hours	21 kWh
<b>Product Data</b>	
Full product code	871869964695000

Order product name	MASTER LEDtube VLE 1500mm HO 20.5W 865 T8
EAN/UPC – product	8718699646950
Order code	64695000
Numerator – quantity per pack	1
SAP numerator – packs per outer box	10
Material no. (12 NC)	929002021902
Net Weight (Piece)	0.270 kg



## Dimensional drawing



Product	D1	D2	A1	A2	A3
MASTER LEDtube VLE 1500mm HO 20.5W 865 T8	25.8 mm	28 mm	1498.7 mm	1505.8 mm	1512.9 mm

## TLED 5ft 220-240V20.5-58W3100lm6500K G13

## Photometric data




## LEDtube 220-240V G13

## LEDtube 220-240V G13 6500k

# Master Value LEDtube T8



## Photometric data




© 2020 Philips Lighting B.V. Page 11

LEDtube 220-240V G13 5ft 3100lm 6500k


## Lifetime



LEDtube 220-240V G13 LumenVsTc



LEDtube 220-240V G13



LEDtube 220-240V G13

LEDtube 220-240V G13 LifetimeVsTc

# Master Value LEDtube T8

## Lifetime



LEDtube 220-240V G13 FailureRate

