



# MASTER LEDspot MV

## MASTER LED spot VLE DT 6.2-80W GU10 927 36D

Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting (track, corridors, lift lobbies, display cases and cabinets) in the hospitality industry. It is particularly suitable to public areas where the light is on 24/7, such as lobbies, corridors, stairwells. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness, enabling hospitality owners to achieve a return on their investment within one year. These LEDspots are compatible with most existing fixtures with a GU10 holder and designed as a retrofit replacement for halogen or incandescent spots. The dimmable versions drive further efficiencies, while helping to create the desired atmosphere.

### Warnings and Safety

- Operating temperature range is between -20° C and 45° C ambient
- Only to apply in dry or damp locations and most of open fixtures with lamp-holders that offer sufficient space (10 mm free air space)
- Not intended for use with emergency light fixtures or exit lights

### Product data

General Information			
Cap base	GU10 [ GU10]	Luminous intensity (nom.)	950 cd
EU RoHS compliant	Yes	Colour designation	Warm White (WW)
Nominal lifetime (nom.)	25000 h	Correlated Colour Temperature (Nom)	2700 K
Switching cycle	50,000X	Luminous efficacy (rated) (nom.)	92.00 lm/W
Technical type	6.2-80W	Colour consistency	<6
		Colour rendering index (nom.)	90
		LLMF at end of nominal lifetime (nom.)	70 %
		Luminous flux in 90° cone (rated)	575 lm
Light Technical		Operating and Electrical	
Colour Code	922-927 [ CCT of 2,200 K-2,700 K]	Input frequency	50 to 60 Hz
Beam Angle (Nom)	36°		
Luminous flux (nom.)	575 lm		

# MASTER LEDspot MV

Power (Rated) (Nom)	6.2 W
Lamp current (nom.)	33 mA
Wattage equivalent	80 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.88
Voltage (Nom)	220-240 V

## Temperature

T-Case maximum (nom.)	75 °C
-----------------------	-------

## Controls and Dimming

Dimmable	Yes
----------	-----

## Approval and Application


Energy efficiency label (EEL)	A++
-------------------------------	-----

Suitable for accent lighting	Yes
Energy consumption kWh/1,000 hours	7 kWh

## Product Data

Full product code	871869966271400
Order product name	MASTER LED spot VLE DT 6.2-80W GU10 927 36D
EAN/UPC – product	8718699662714
Order code	66271400
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
SAP material	929002065902
SAP net weight (piece)	0.040 kg


## Dimensional drawing




GU10 7.5-80W 650lm 2700K GU10 D 15khrs

Product	D	C
MASTER LED spot VLE DT 6.2-80W GU10 927 36D	50 mm	56 mm

## Photometric data




GU10 7.5-80W 650lm 2700K GU10 D 15khrs



GU10 7.5-80W 650lm 2700K GU10 D 15khrs


# MASTER LEDspot MV

## Photometric data




GU10 7.5-80W 650lm 2700K GU10 D 15khrs

## Lifetime



GU10 7.5-80W 650lm 2700K GU10 D 15khrs



GU10 7.5-80W 650lm 2700K GU10 D 15khrs

